



Profometer Corrosion Potential PM8500

The most complete half-cell solution for rapid on-site mapping of corrosion potential



Productivity

Boost your productivity up to 40 times faster than any other rod electrode on the market using our unique wheel electrodes



Ergonomics

Compact, ultra-light and wireless for comfortable measurements in all types of concrete elements



Onsite Data

Best-in-class app for corrosion assessment with several views for easy data evaluation and interpretation



Profometer App Corrosion Tech Specs

Display Unit	Any compatible Apple iPad (iOS 11.0 and higher)
Scanning Options	• Scan with a fixed grid or flexible grid • Scan horizontally or vertically • Scan forwards or negative • Return to start for each new line or scan in an S-pattern • Select any cell and continue scanning from there • Start a scan from any corner • Set and maintain zoom level while scanning • Skip a preset distance • Open a previous scan and continue scanning from any cell
Export formats	• JPG (Screenshot) • PNG • CSV • HTML • DXF
Display Unit Specs*:	• Latest Apple® iPad recommended (iPad with iOS 11.0 and higher) • Screen size: From 7.9" to 12.9" • Resolution: Up to 2732-by-2048 • Memory: Up to 2TB • Weight: Down to 301 g / 10.6 oz • Camera: Up to 12MP Wide and 10MP Ultra Wide • Optional: USB-C, 5G, Face ID
Display Unit Sensors*:	• LiDAR Scanner (optional) • Three-axis gyro • Accelerometer • Ambient light sensor • Barometer • Built-in GPS/GNSS

* Depending on iPad model iPad is a trademark of Apple Inc.;
iOS is a registered trademark of Cisco in the US and is used by
Apple under license



Instrument Tech Specs

Technology	Half Cell Potential
Measured Quantity	Corrosion potential in millivolts [mV]
Connection	Wireless - Bluetooth
Cover Measuring depth	First rebar layer
Voltage Measurement Range	-3000mV to +3000mV
Resolution	+/-1mV
Input Impedance	100MOhm
Encoder Accuracy	+/- 0.5 mm / 0.02 in + 0.78% of measured length Resolution: 3.3 mm / 0.13 in (128 steps / rotation)
Max Scanning Speed	1 m/s - 3.3 ft/s
Max Area Scan	100 x 100 m - 330 x 330 ft

Dimensions

Sensor unit	(127 x 59 x 56)mm / (5 x 2.3 x 2.2)in without holder (127 x 98 x 72)mm / (5 x 3.9 x 2.8)in with holder
Rod electrode	D= 36mm x 155mm / D=1.4 in x 6.1 in with protection-cap
One wheel electrode	(194 x 138 x 127)mm / (7.6 x 5.4 x 5)in without telescopic rod (2000 x 138 x 127)mm / (78.7 x 5.4 x 5)in with extended telescopic rod (700 x 138 x 127)mm / (27.6 x 5.4 x 5)in with pulled in telescopic rod
Four wheel electrode	(830 x 350 x 140)mm / (32.6 x 13.8 x 5.5)in without telescopic rod (2150 x 830 x 140)mm / (84.6 x 32.6 x 5.5)in with extended telescopic rod (840 x 830 x 140)mm / (32.8 x 32.6 x 5.5)in with pulled in telescopic rod

Weight

Sensor unit	150g / 0.33 lbs without holder 220g / 0.49 lbs with holder
Rod electrode	120g / 0.26 lbs without cable / without copper sulfate, without Interface-Box
One wheel electrode	2000g / 4.41 lbs without fluid, with interfacebox an telescopic rod + 435g / 0.96 lbs including fluid
Four wheel electrode	6900g / 15.2 lbs without fluid + 435g / 0.96 lbs per wheel including fluid
Standard kit (all items including carrying case)	7400g / 16.3 lbs
One wheel kit (all items including cartoon box)	2900g / 6.39 lbs
Four wheel kit (all items including carrying case)	17660g / 38.93 lbs
Battery	1xAA (NiMH) rechargeable or non rechargeable Removable Flight-safe 8 Hours autonomy USB-C charger
Environmental Conditions	Humidity <95% RH, non-condensing Operating temperature: -10°C to +50°C

Our Accessories

Image	PartNumber	Description
	39260330	Ball joint accessory for the one-wheel electrode to connect to the telescopic rod for more flexible measurements.

Standards & Guidelines	Description
ASTM C 876-15	
DGZfP B3	
JGJ/T 152 (China)	
JSCE E 601	
RILEM TC 154-EMC	
SIA 2006 (Switzerland)	
UNI 10174	
ODM 218.3.001-2010	

Authorized Distributor



NL SCIENTIFIC INSTRUMENTS SDN. BHD. (881121-P)
No. 16, Lorong Sungai Puloh 1A/KU6,
Taman Teknologi Gemilang,
Kawasan Perindustrian Sungai Puloh,
42100 Klang, Selangor, Malaysia.

Email
sales@nl-test.com

Hotline
+603-3884 6088

Website
www.nl-test.com

